

1999 Hoppmann 30-Head Plug Turret 3

Mfg: Hoppmann

Model: Turret

Stock No. EMFP004.

Serial No. 364044

1999 Hoppmann 30-Head Plug Turret 3. Model: Turret. S/N: 364044. Previously used to plug Crayola marker ends. Operates on vacuum air and mechanical pressure. Designed for a line speed of 600 ppm; capable of running at approximately 630 ppm. Plug dimensions: 5/8 in. dia. x 5/8 in. H. Marker carrier dimensions: 1-1/2 in. outer diameter x 1-3/4 in. H (with 5/8 in. inner diameter). Marker dimensions (unplugged): 5/8 in. dia. x 4-1/2 in. H. Height at conveyor inlet/outlet: 33-1/2 in. Belt width: 2-1/2 in. Baldor Industrial Motor, 1 hp, 1725 rpm, 208-230/460 V, 3.7-3.4/ 1.7 amps, 60 Hz, 3 phase. Boston 700 Series Gear Drive, 40 ratio, 43.125 rpm (final). Overall dimensions: 60 in. L x 48 in. W x 78 in. H. Duro-United and Numatics Air Regulators for: turret main air, air clutch, and vacuum air. (10) Festo Pneumatic Vacuum Generators, Model: VAK-114 6890.

(9) Banner Mini Beams, Model: SM312FQD for: plug presence, assembly height, plug not taken, assembly presence, exit jam max level, puck clock, height inspection, and fault reject. Solenoids for: main air, brake, clutch, plug presence, plug eject, clock, motor node, and drive. (1) Suco low air pressure sensor.









