

2000 Hoppmann 55-Head Centrifugal Feeder

Mfg: Hoppmann

Model: FRS60SS

Stock No. ENAE002.

Serial No. RS60XXXDSA00010

2000 Hoppmann 55-Head Centrifugal Feeder. Model: FRS60SS. S/N: RS60XXXDSA00010. Applications: orients 2.6 oz. and 1.6 oz. deodorant stick containers. Baldor Industrial Motor, 3/4 hp, 1750 rpm, 90 V, 7.6 amps. Bonfiglioli Speed Reducer, 100 ratio, 17.5 rpm (final). Hoppmann's FRS-60 is specifically designed to feed a wide range of large bottles and parts. The delivery rates vary from moderate to high speed depending on part characteristics. The FRS-60 is engineered to interface with Hoppmann prefeeders, accumulating conveyors, assembly systems and other downstream equipment, aluminum bowl with stainless steel walls, polyurethane scallops, polycarbonate hinged top cover. Inlets: (1) 25-1/2 in. L x 25-1/2 in. W infeed chute. Overall dimensions: 96 in. L x 94 in. W x 76 in. H.







