

2001 Fristam Pump

Mfg: Fristam

Model: FKL25

Stock No. HDDF121D.

Serial No. FKL250201662

2001 Fristam Pump. Model: FKL25. S/N: FKL250201662. Maximum speed: 600 rpm, Maximum pressure: 300 psi. Pump capacity: 33.549 gpm @ 600 rpm (0.053 gal/rev), final rpm: 633. Balanced rotor allows for higher pressures, highly efficient and durable, all seals retrofitable in the field, Universal mounting, CIP-able and SIP-able. Applications: dairy products, food & food processing, beverage & brewery, baking/confection, pharmaceutical & cosmetics, food & food processing, meat & poultry. U.S. Unimount 125 motor, 5 hp, 1745 rpm, 208-230/460 V, 15-13.6/6.8 FL amps, 16.7/8.35 SF amps, 60 Hz, 3 phase. Pump inlet/outlet: 1-1/2 in. 'S' line. Overall dimensions: 38 in. L x 18 in. W x 19 in. H.



