

## Stainless Steel Incline Elevator

Mfg:

Model:

Stock No. ENAE005.

Serial No.:

Stainless Steel Incline Elevator. Infeed hopper dimensions: 4 ft. L x 4 ft. H. Belt width: 20 in. Maximum aperture/clearance above belt: 20 in. W x 4 in. H. Cleat height: 4 in. Distance between cleats: 12 in. Baldor DC Motor, 1/2 hp, 1750 rpm, 90 V, 5.1 amps. Indiana Power Transmission Systems Inc., 30 ratio, 58.3 rpm (final). Elevator infeed height: 3 ft. 9 in. Elevator exit height: 6 ft. 1-1/2 in. Inlets: (1) 4 ft. L x 2 ft. 9 in. W infeed. Outlets: (1) 1 ft. 8 in. L x 1 ft. 2 in. W discharge. Overall dimensions: 7 ft. 8 in. L x 4 ft. 2-1/2 in. W x 8 ft. 7 in. H.







