

Howden WRV 204/1.93 Rotary Screw Compressor Package - 400 HP

Mfg: Howden

Model: WRV 204/1.93

Stock No: HDFA367.35

Serial No: MK5E – 165

Howden WRV 204/1.93 Rotary Screw Compressor Package. Model: WRV 204/1.93. S/N: MK5E-165. Job No: 560-22968. Refrigerant: Last used with R-717 (ammonia). Leak test pressure: 317 psig. Hydrostatic test pressure: 470 psig. Vi setting: 3.6. Displacement: 962 cfm. 1990 Vilter oil separator, S/N: 3-02035-2, shell side MAWP: 300 psig at 400°F, shell side MDMT: -20°F at 300 psig. Vilter microprocessor control system, power supply: 115 V. Toshiba motor, 400 hp, 3540 rpm, 460 V, 470 amps, 60 Hz, 3 phase. 2000 Imo Industries Inc. rotary positive displacement pump, Series: 3E, P/N: 3242/374 D3ENC-162, S/N: L3365-3. Leeson motor, 5 hp, 3510 rpm, 208-230/460 V, 12.8-12/6 FLA, 60 Hz, 3 phase. Ram starter control panel. Panel dimensions: 2 ft. 7 in. L x 1 ft. 7 in. W x 5 ft. 6 in. H. Inlets: (1) 5 in. dia. refrigerant suction port. Outlets: (1) 1 in. dia. safety relief port, (1) 4 in. dia. refrigerant discharge port. Overall dimensions: 14 ft. 1 in. L x 4 ft. 5 in. W x 8 ft. 10 in. H. (ACN524-BC/motor/starter).









