

1999 Hoppmann Centrifugal Feeder

Mfg: Hoppmann

Model: FT50-2

Stock No. ENAE58346B.

Serial No. 37391b

1999 Hoppmann Centrifugal Feeder. Model: FT50-2. S/N: 37391b. Previously used to feed 1.7 oz. and 2.7 oz. deodorant screw caps. Hoppmann's FT-50 rigid disc centrifugal feeder is specifically designed to feed and orient large parts. This feeder incorporates a patented combined disc and rim drive system. This assures tight bowl/disc gap operating tolerances. The delivery rates vary from moderate to high speeds depending on part characteristics. Materials of construction: aluminum bowl with Teflon hardcoat anodized finish, FDA approved heavy gauge ABS plastic center disc, 304 stainless steel construction, epoxy powder coated finish, single motor drive system, metric components. (2) Baldor DC Motors, 0.75 hp, 1750 rpm, 90 V, 7.6 amps. Boston Gear Speed Reducer, 40 ratio, 43.75 rpm (final). Bonfiglioli Speed Reducer, 100 ratio, 17.5 rpm (final). Conveyor infeed height: 77 in. Conveyor exit height: 47 in. Inlets: 19 in. L x 15 in. W infeed chute. Outlets: 8 in. L x 5 in. W discharge chute. Overall dimensions: 156 in. L x 73 in. W x 77 in. H.

1998 Hoppman Gravity Rollers, Model: GRAV ROLLERS, S/N's: 33411 and 33412, roller dimensions: 1-1/4 in. dia. x 48 in. L. (2) Bodine DC Motors, 1/8 hp, 2500 rpm, 130 DCV, 0.91 amps.





