

FES Ammonia Twin-Screw Compressor

Mfg: FES

Model: 575B-LE

Stock No. HDKF726.45

Serial No. 2512506

FES Ammonia Twin-Screw Compressor. Model: 575B-LE. S/N 2512506. Leak pressure: 313 psig. Hydrostatic pressure: 470 psig. Compressor run time: 78576 hrs. Toshiba Motor, 200 hp, 3540 rpm, 460 V, 470-235 amps, 60 Hz, 3 phase. Inlets: (1) 8-1/2 suction tube with a 13-1/2 in. dia. flange and (8) 3/4 attachment holes at a center-to-center distance of 13 in. Outlets: (1) 4-1/2 in. dia. discharge pipe. Overall dimensions: 12 ft. 6 in. L x 64 in. W x 9 in. H.

FES Oil Separator, S/N: 86033, Nat'l Bd: 2565, MAWP: 250 psi, maximum temperature: 200 °F. FES Oil Cooler, S/N: TS 18, Nat'l Bd: 12356, MAWP: 250 psi, maximum temperature: 200 °F, shell side MAWP @ 200° F: 400 psi, tube side MAWP @ 200° F: 250 psi. Viking Rotary Pump, Model: AV427AK, S/N: 2389062. FES Micro II Controls with touchpad controls and digital display.



