Frick RXB-39 Rotary Screw Compressor Package - 125 HP	
Mfg: Frick	Model: RXB-39
Stock No.: GCDM01.15	Serial No.: XJS120L0183F

Frick RXB-39 Rotary Screw Compressor Package - 125 HP. Frick compressor model: XJS120L0183F. Refrigerant types: NH3/R22. Volume ratio: 2.2-5.0, Max Speed 4700 RPM. Max Design Pressure: 362 PSI. Nominal rating: 73.8 TR / 91 BHP at +20F suction / 95F condensing (R-22). At -40F suction: 17.8 TR / 64.6 BHP (R-22). Frick RXB Control Panel. Includes compressor starter / disconnect panel. Previously used with R-22 refrigerant for equipment testing. Removed in running condition. Overall dimensions: 8 ft. L x 4 ft. 9 in. W x 6 ft. 8 in. H.









UNIT MODEL NO. UNIT SER. NO. FRICK SALES ORD.	
REFRIGERANT	
MAX. SPEED RPM	SOUTH OF STREET
MAX. DESIGN PSIG PRESSURE KPa	
WAYNESBORO,	PA. 17268













