

Keenline 48 in. Loading/Unloading Turntable

Mfg: Keenline

Model:

Stock No. 18.GM403.6

Serial No.:

Keenline 48 in. Loading/Unloading Turntable. Stainless steel construction. Height at conveyor infeed/exit: 37 in. Provides an effective means of loading/unloading objects onto a production line. Reliance Electric Motor, 1/2 hp, 1725 rpm, 208-230/460 V, 1.5-1.5/.75 amps, 60 Hz, 3 phase. Dodge Tigear Speed Reducer, 40 ratio, 43 rpm (final). Overall dimensions: 48 in. dia. x 36-1/2 in. H.



