

Waukesha 30 Positive Displacement Pump

Mfg: Waukesha

Model: 30

Stock No. HDPH641.4a

Serial No. 158779-95

Waukesha 30 Positive Displacement Pump. Model: 30. S/N: 158779-95. Pumping capacity: 5.24 gpm. Displacement per revolution: 0.060 gal. Nominal capacity: 36 gpm. Maximum speed: 600 rpm. Reliance Electric Motor, 1-1/2 hp, 1750 rpm. Nord Gear Drive, 20.01 ratio, 87.45 rpm (final). 3-A Sanitary rated. 316 stainless steel body, cover and shafts. Components can be easily disassembled for COP cleaning. Typical applications: bakery, beverage, canning, confectionary, cosmetics, dairy, meat packing, pharmaceutical and aseptic. Inlets/outlets: (2) 1-1/2 in. dia. S-line fittings. Overall dimensions: 40 in. L x 14-1/2 in. W x 16 in. H.



