

Tri Clover PRE25 Positive Pump

Mfg: Tri Clover

Model: PRE25-11/2M-TC1-4-SL-S

Stock No. HDPW833.3

Serial No. P8052J

Tri Clover PRE25 Positive Pump. Model: PRE25-11/2M-TC1-4-SL-S. S/N: P8052J. Maximum capacity: 28 gpm @ 28 psi. Displacement @ 100 rpm: 8.0 gallons. Single mechanical seals. The PR line was designed to handle liquids and semi-solids with entrained vapors. It performs effectively for suction lift service and reduces maintenance costs and downtime. For operations such as: liquid sugar, tacky products like corn syrup, and viscous products. Overall dimensions: 14-1/2 in. L x 7 in. W x 11 in. H.

