

## Evapco Evaporative Condenser- 315 Ton

Mfg: Evapco

Model: LSCB-315

Stock No. GPS2001.100

Serial No. 5132070

Evapco Evaporative Condenser Unit- 315 Ton. Model: LSW-87A. S/N: 5132070. Belt No: B-92. Refrigerant: R-22. Capacity: 500 gpm (30,000 gph) of water from 103 °F - 91 °F @ 75 °F wet bulb. This was shipped from the factory as a Evapco Fluid Cooler, Model LSW-87A, S/N: 5132070, but essentially the same as an LSCB-315 if rated as an evaporative condenser. G-235 Hot dip galvanized steel construction. Manway: 21 in. diameter. (9) Eliminators: 20 in. L x 5 in. W x 70 in. H. LSW series centrifugal fan forced draft units are recommended for a wide range of applications especially where noise is a concern. Inlets: (1) 4 in. diameter PVC pipe, (2) 4-1/2 in. dia. media pipes. Outlets: (1) 4 in. diameter PVC pipe, (2) 4-1/2 in. dia. media pipes. Overall dimensions (complete machine): 18 ft. 8 in. L x 85 in. W x 115 in. H. ACN400.

Baldor Industrial Fan Motor: 25 hp, 208-230/4640 V, 64-60/30 amps, 1760 rpm, 60 Hz, 3 phase.

Pulley ratio: 2-1/2 to 1, final rpm: 704. (6) Centrifugal Fans: 9 in. diameter x 18-1/2 in. W. U.S. Motor (pump): 2 hp, 1725 rpm, 208-230/460 V, 6.2-6.0/3.0 amps, 3 phase. Pump impeller: 5.31 in. diameter.





