

| MODEL | ROWS DEEP | FPI | CAPACITY DATA BTUH/°TD | | CFM | SURFACE (FT ²) | NO. FANS | MOTOR HP | COIL VOLUME (FT ³) | APPROX. SHIPPING WEIGHT |
|--------|-----------|-----|------------------------|--------|--------|----------------------------|----------|----------|--------------------------------|-------------------------|
| | | | LR | DX | | | | | | |
| CO 118 | 4 | 4 | 1,550 | 1,330 | 2,540 | 304 | 1 | 1/4 | .6 | 650 |
| | 6 | 4 | 2,010 | 1,730 | 2,500 | 457 | | | .9 | 750 |
| | 8 | 4 | 2,250 | 1,940 | 2,440 | 609 | | | 1.2 | 840 |
| | 4 | 6 | 1,960 | 1,690 | 2,490 | 444 | | | .6 | 755 |
| | 6 | 6 | 2,290 | 1,970 | 2,400 | 666 | | | .9 | 905 |
| | 8 | 6 | 2,430 | 2,090 | 2,320 | 888 | | | 1.2 | 1,050 |
| CO 218 | 4 | 4 | 2,930 | 2,520 | 4,990 | 554 | 2 | 1/4 | 1.0 | 895 |
| | 6 | 4 | 3,770 | 3,240 | 4,870 | 831 | | | 1.5 | 1,050 |
| | 8 | 4 | 4,300 | 3,700 | 4,750 | 1,109 | | | 2.0 | 1,210 |
| | 4 | 6 | 3,730 | 3,210 | 4,910 | 808 | | | 1.0 | 1,085 |
| | 6 | 6 | 4,370 | 3,760 | 4,700 | 1,211 | | | 1.5 | 1,335 |
| | 8 | 6 | 4,660 | 4,010 | 4,520 | 1,616 | | | 2.0 | 1,590 |
| CO 318 | 4 | 4 | 3,860 | 3,320 | 7,120 | 673 | 3 | 1/4 | 1.1 | 965 |
| | 6 | 4 | 5,040 | 4,330 | 6,900 | 1,010 | | | 1.7 | 1,250 |
| | 8 | 4 | 5,650 | 4,860 | 6,560 | 1,347 | | | 2.3 | 1,560 |
| | 4 | 6 | 4,880 | 4,200 | 6,980 | 981 | | | 1.1 | 1,195 |
| | 6 | 6 | 5,830 | 5,010 | 6,580 | 1,472 | | | 1.7 | 1,600 |
| | 8 | 6 | 6,200 | 5,330 | 6,210 | 1,962 | | | 2.3 | 2,020 |
| CO 418 | 4 | 4 | 5,010 | 4,310 | 9,360 | 863 | 4 | 1/4 | 1.5 | 1,105 |
| | 6 | 4 | 6,540 | 5,620 | 9,100 | 1,295 | | | 2.2 | 1,550 |
| | 8 | 4 | 7,400 | 6,360 | 8,600 | 1,727 | | | 2.9 | 1,950 |
| | 4 | 6 | 6,340 | 5,450 | 9,190 | 1,257 | | | 1.5 | 1,465 |
| | 6 | 6 | 7,570 | 6,510 | 8,650 | 1,886 | | | 2.2 | 1,995 |
| | 8 | 6 | 8,080 | 6,950 | 8,130 | 2,514 | | | 2.9 | 2,540 |
| CO 324 | 4 | 4 | 7,350 | 6,320 | 13,340 | 1,296 | 3 | 1/3 | 2.2 | 1,520 |
| | 6 | 4 | 9,350 | 8,040 | 12,550 | 1,943 | | | 3.2 | 1,900 |
| | 8 | 4 | 10,500 | 9,030 | 12,050 | 2,591 | | | 4.3 | 2,220 |
| | 4 | 6 | 9,270 | 7,970 | 13,040 | 1,887 | | | 2.2 | 1,965 |
| | 6 | 6 | 11,000 | 9,460 | 12,290 | 2,830 | | | 3.2 | 2,565 |
| | 8 | 6 | 11,650 | 10,020 | 11,580 | 3,774 | | | 4.3 | 3,165 |
| CO 424 | 4 | 4 | 9,080 | 7,810 | 17,190 | 1,562 | 4 | 1/3 | 2.6 | 1,750 |
| | 6 | 4 | 11,720 | 10,080 | 16,320 | 2,344 | | | 3.9 | 2,210 |
| | 8 | 4 | 13,300 | 11,440 | 15,470 | 3,126 | | | 5.1 | 2,670 |
| | 4 | 6 | 11,520 | 9,910 | 16,780 | 2,276 | | | 2.6 | 2,285 |
| | 6 | 6 | 13,690 | 11,780 | 15,660 | 3,414 | | | 3.9 | 3,010 |
| | 8 | 6 | 14,530 | 12,500 | 14,670 | 4,552 | | | 5.1 | 3,740 |
| CO 524 | 4 | 4 | 11,350 | 9,760 | 21,490 | 1,953 | 5 | 1/3 | 3.2 | 2,190 |
| | 6 | 4 | 14,650 | 12,600 | 20,400 | 2,930 | | | 4.8 | 2,650 |
| | 8 | 4 | 16,230 | 13,960 | 19,340 | 3,908 | | | 6.4 | 3,340 |
| | 4 | 6 | 14,200 | 12,380 | 20,070 | 2,845 | | | 3.2 | 3,010 |
| | 6 | 6 | 17,120 | 14,720 | 19,570 | 4,268 | | | 4.8 | 3,650 |
| | 8 | 6 | 18,160 | 15,620 | 18,330 | 5,690 | | | 6.4 | 4,675 |