

## FES/Dunham-Bush Screw Compressor Package

Mfg: FES/Dunham-Bush

Model: 95

Stock No. HBSV001.

Serial No. 4496

FES/Dunham-Bush Screw Compressor Package. Model 95. S/N: 4496. Leak pressure: 313 psi. Hydrostatic pressure: 471 psi. Inlets: (1) 4 in. dia. suction pipe. Outlets: (1) 2 in. dia. discharge pipe. Overall dimensions: 10 ft. 10 in. L x 49 in. W x 96 in. H. (Note: Compressor does not include motor). FES Micro Master Control Panel, Model: Retrofit, S/N: 93013101, Contract No: 93013101. Oil Separator, MAWP @ 300 °F: 300 psi, MDMT @ 300 psi: - 20 °F, head radius: 2:1, head thickness: 0.312 in., shell thickness: 0.312 in. Viking Rotary Pump, Model: AV426AS, S/N: 1014908. Teco Motor, 3 hp, 1170 rpm, 230/460 V, 9.4/4.7 amps, 60 Hz, 3 phase. Dunham Bush Shell & Tube Heat Exchanger, Model: C00SF1529, shell side MAWP: 350 psig, tube side MAWP: 150 psig. Starter included.

