

Cleaver Brooks Spraymaster Deaerator- 800 Gallons

Mfg: Cleaver Brooks

Model: SM30

Stock No. HD-SC294.16a

Serial No. DS-3660

Cleaver Brooks Spraymaster Deaerator- 800 Gallons. Model: SM30. S/N: DS-3660. Nat'l Bd: 53121. MAWP: 50 psi @ 650 °F. Shell thickness: 0.250 in. Head thickness: 0.312 in. (2) Pressure relief valves. Oval manway: 15 in. L x 11 in. W. Tank dimensions: 103 in. L x 48 in. dia. (2) Centriflo pumps, Type 618-D8-F, capacity: 120 gpm (each). US Motor, 25 hp, 3520 rpm, 230/460 V, 62.0/31.0 amps, 60 Hz, 3 phase. Leeson Motor, 25 hp, 3500 rpm, 208-230/460 V, 64-62/31 amps. Inlets/outlets: (2) 2-1/2 in., (2) 1/2 in., (1) 5 in., (3) 2 in. Overall dimensions: 11 ft. 6 in. L x 54 in. W x 80 in. H.

