

## Ceia Metal Detector

Mfg: Ceia

Model: THS-FB/1

Stock No. HDAF614.22a

Serial No. 20200209005

Ceia Metal Detector. Model: THS-FB/1. S/N: 20200209005. Dimensions: 13 in. x 7 in. (350 mm x 175 mm). Maximum aperture/clearance: 10-1/2 in. W x 5-1/2 in. H. Tested. Power supply: 115/230 V, 50/60 Hz, 60 VA. Belt width: 12 in. Baldor Washdown Duty Motor, 3/4 hp, 1725 rpm, 115/230 V, 8/4 amps, 60 Hz, 3 phase. Morse Raider Gear Reducer, 30 ratio, 57.5 rpm (final). The THS is an extremely compact metal detector with very high sensitivity, controlled by a microprocessor and designed for industrial use. Applications include packaged or loose product. Conveyor infeed/exit height: 32 in. Overall dimensions: 50 in. L x 34 in. W x 49 in. H. (ACN85a).









