

WAUKESHA Series 200 CENTRIFUGAL PUMPS

● = Best Efficiency Point
 % = Efficiency Percentage

CAPACITY CURVES


Based on water at 70°F. (22°C.)

MODEL: 2085

60 Hz

1750 RPM

SIZE: 3 x 2-1/2 x 8.7



NOTES

- ① Impeller diameters available in 1/16-inch increments
- ② NPSHR is shown for maximum impeller diameter

COMMON CONVERSIONS

- ③ $PSI = \frac{\text{Head in Feet} \times \text{Specific Gravity}}{2.3}$
- ④ $Kg/cm^2 = \frac{\text{Head in Meters} \times \text{Specific Gravity}}{10}$
- ⑤ $HP \times 0.746 = Kw$



611 Sugar Creek Road Delavan, WI 53115
 Phone: 800-252-5200 or 262-728-1900
 Fax: 800-252-5012 or 262-728-4904
 www.gowcb.com

CURVE NUMBER
95-07006

EFFECTIVE DATE
 5-31-2002

PAGE NUMBER
 006