

Hoffman Control Panel

Mfg: Hoffman

Model:

Stock No. RWDG269.

Serial No.

Hoffman Control Panel. Cat #: A-181610CHSCFG. Components: Allen-Bradley (AC inputs, Relay outputs, AC power) box. (1) ASCO air valve (100 psi). (2) Speed control air valves: (1) 50 psi, (1) 30 psi. Meanwell box, input: 100-240 Vac, 50-60 Hz, output: +24 V, 5 in. W x 6 in. L. Electrical box. 3-way switch: mode select, homogenizer power, homogenizing pressure. Overall dimensions: 16 in. L x 11 in. W x 22 in. H.

