

## SECO Simplimatic Engineering Company Conveyor

Mfg: SECO

Model:

Stock No. HDBA042B.

Serial No.:

SECO Simplimatic Engineering Company Conveyor. Baldor Motor, 1 hp, 1725 rpm, 208-230/460 V, 3.6-3.2/1.6 amps, 60 Hz, 3 Phase. Flexaline Grove Gear, 1.02 Hp Input, Ratio: 80. Infeed/Exit: 49 in. H. Product Clearance: 24 in. W x 16-1/2 in. H. (4) 6 in. dia. sprocket with a 3/4 in. spacing between teeth. Overall Dimensions: 10 ft. 3 in. L x 34 in. W x 79 in. H.





