

## SECO Simplimatic Engineering Company Conveyor

Mfg: SECO

Model:

Stock No. HDBA042.33a

Serial No.:

SECO Simplimatic Engineering Company Conveyor. Product clearance: 5-1/2 in. W x 13 in. H. Includes (2) 6 in. dia. sprockets with a 3/4 in. tooth pitch. Baldor Motor, 1/2 hp, 1725 rpm, 208-230/460 V, 1.8-1.6/.8 amps, 60 Hz, 3 phase. Flexaline Grove Gear, Ratio: 40, 43.125 rpm (final). Conveyor infeed/exit height: 48 in. Overall dimensions: 49 in. L x 21 in. W x 77 in. H.

