

Stainless Steel Barrel Lift Station


Mfg:



Model:

Stock No. JMB005a

Serial No.:

Stainless Steel Barrel Lift Station. Infeed roller conveyor. Number of rollers: 5. Roller dimensions: 3 dia. x 2 ft. L rolls. Basket dimensions: 2 ft. L x 2 ft. W x 3 ft. H. U.S. Electric Motor, 2 hp, 1730/1405 rpm, 208-230/460-190/380 V, 6.0/3.0-6.8/3.4 amps, 60/50 Hz, 3 phase. Conveyor infeed/exit height: 1 ft. Overall dimensions: 6 ft. L x 3 ft. 4 in. w x 9 ft. 3 in. H.





Do not use eyebolts or lifting hooks to lift anything except the product. 931900

MODEL	R471A	FR	1451C	ENCL	TE	TYPE	FUT	PH	3
SHAFT END SPS	6205-2Z-J/C3	DRP END SPS	6203-2Z-J/C3	MAX	40 °C	DUTY CONT.			
ID#	B11 01029508	001	F	TEMP CLASS	F	USABLE ON 208V 60HZ AT MAX AMPS 6.9			
HP	2.0	RPM	1730	CODE	L	DES	B	VOLTS	208-230/460
60 HZ DATA	AFMS NOM EFFICIENCY 84.0	GUARANTEED EFFICIENCY 81.5	FL AMPS 6.1	FL AMP 6.0	SP	1.25	SP AMP 7.0	SP AMP 3.5	
MAX KVAR	0.9	NOM PF	75.8	SP	1.25	SP AMP	7.0	SP AMP	3.5
HP	2.0	RPM	1405	CODE	H	DES	B	VOLTS	190 / 380
50 HZ DATA	AFMS NOM EFFICIENCY 80.0	GUARANTEED EFFICIENCY 77.0	FL AMPS 6.8	FL AMP 3.4	SP	1.0	SP AMP		
MAX KVAR	1.0	NOM PF	82.6	SP	1.0	SP AMP			







U.S. ELECTRICAL MOTORS
DIVISION OF EMERSON ELECTRIC CO.
ST. LOUIS, MO
MADE IN U.S.A.

ENERGY EFFICIENT MOTOR
96773R