

3M-Matic 120AF Case Sealer System

Mfg: 3M-Matic




Model: 120AF

Stock No.: HDBF079.12

Serial No.: 6033

3M-Matic 120AF Case Sealer System. Model: 120AF. Type: 19600. S/N: 6033. Capacity: up to 27 packages per minute. Minimum box size: 6 in. L x 4-3/4 in. W x 4-3/4 in. H. Maximum box size: 2 ft. 1 in. L x 1 ft. 8 in. W x 1 ft. 8 in. H. Box weight range: 4 lbs. to 65 lbs. Tape size: 1.5 in. to 2 in. W. Power supply: 115 V, 3.8 amps, 60 Hz. (2) Bodine electric drives, 1/9 hp, 1700 rpm, 60 Hz, 1.4 amps, single phase. Conveyor dimensions: 4 ft. 10 in. L x 8 in. W. Conveyor infeed/exit height: 1 ft. 10 in. Overall dimensions: 6 ft. 4 in. L x 3 ft. 3 in. W x 5 ft. 3 in. H. (ACN123a)





Matic™ **3M**

120af

Adjustable Case Sealer

Type 19600 Ser. No. 05153

Made in Italy

115 Volts	2.8 Amps	NRTL SP
60 Hz	320 Watts	

CHICAGO 60618, U.S.A.

BODINE
ELECTRIC
COMPANY

Small Motor

TYPE 34X65FC1

NO T0787078

VOLTS 115 PH 1

AMP 4 HZ 60

HP 1/2

RPM 1700

CAP 12.5 MFD

DUTY CONT FF

INS 105 AMB 40 90

WARNING

MOVING FLAP KICKER
CAN CAUSE BODILY INJURY
KEEP AWAY FROM THIS AREA