

FES 180B/95 / Dunham-Bush 1610 / Mycom 200SUD Dual Compressor Package – 100 / 60 HP

Mfg: FES / Dunham-Bush / Mycom

Model: 180B/95 / 1610 /200SUD

Stock No: HDCD344C.45a

Serial No: 77-064-61

FES 180B/95 / Dunham-Bush 1610 / Mycom 200SUD Dual Compressor Package. Model: FES 180B/95 / Dunham-Bush 1610 / Mycom 200SUD. S/N: 77-064-61. Dual compressor package with (1) Louis-Allis motor, 60 hp, 3600 rpm, 460 V, 60 Hz, 3ph and (1) Louis-Allis motor, 100 hp, 3600 rpm, 460 V, 60 Hz, 3ph. FES oil separator, N/B: 298, FES no. 77064, MAWP: 250 psi, 300°F Max. Temperature, -20°F Min.Temp, inlet: 2-½ in. port., outlets: 1-¼ in. w port and 1 in. w port, (3) Watlow oil heaters. (1) Mycom booster compressor: Model 200SUD. S/N: 2052095. Nominal capacity: Last used with R-717 producing 48.5 tons with a -45°F suction temperature and a 95°F discharge temperature. Vi setting: 2.6. Displacement: 571 cfm. (1) Dunham-Bush high stage compressor: Model: 1610. S/N: 1610DLA3VOD X1958. Nominal capacity: Last used with R-717 producing 67.9 tons with a -45°F suction temperature and a 95°F discharge temperature. Vi setting: 4.15. Displacement: 278 cfm. Overall dim: 17 ft. 10 in. L x 4 ft. 10 in. W x 6 ft. 10 in. H.









