

## FES / Dunham - Bush Screw Compressor Package – 200 HP

Mfg: FES / Dunham - Bush

Model: 550-B/ 2516

Stock No: JSKS03

Serial No: 79-0180-0305

FES / Dunham - Bush Screw Compressor Package. Model: 550-B / 2516. Serial number 79-0180-0305. FES contract number: 79-0180-0305-09. Capacity rating: 217 tons at 192 BHP using R-717 (ammonia). Dunham - Bush compressor, model: 2616, no. 3031. Leak test pressure 313 psig, Hyd. test pressure: 470. Displacement 1668 cfm. Toshiba World Energy Series, 3-phase induction motor: Model: B2002VLG3UD ODP, Serial number: 6200111, 200 hp, 3540 rpm 3 phase, 60 Hz. Design: B, 230/460V amps: 470/235, service factor: 1.15, frame size: 4441s, continuous duty, drip proof enclosure type: TIKK. Oil separator: FES no. 79158. National Board no: 805, MAWP: 250 psi, MDMT 300 psi MAWT: -20F, HD RAD 2:1, HD TK.375, SHL TK.375. Also features an oil pump package and a De Laval Barksdale Temperature switch: Switch number ML1H-H204-WS. Media temperature limits: from -100F to 250F. Hours on compressor: 8453. Overall dimensions: 12 ft. 9-1/2 in. L x 2 ft. 7-1/2 in. W x 8 ft.H.







