

1991 Fristam FPX-Series Centrifugal Pump

Mfg: Fristam

Model: FPX1732-160

Stock No.: HDCF175.7

Serial No.: 132171075

1991 Fristam FPX-Series Centrifugal Pump. Model: FPX1732-160. S/N: 132171075. Flow rate for new pump is 225 gpm with required horsepower and pressure. Impeller diameter: 5 ½ in. or 160mm. Seal option: single, mechanical. Baldor industrial motor, 15 hp, 3500 rpm, 208-230/460 V, 37.5-34/17 amps, 60 Hz, 3 phase. Inlets: (1) 2-1/2 in. dia. S-line fitting. Outlets: (1) 2 in. dia. S-line fitting. Capable of delivering high volumes and high pressures while handling shear sensitive products, it is the pump of choice for products with viscosities up to 600 cps and process temperatures up to 400°F. The FPX series is well known for quiet, efficient, low maintenance operations. Overall dimensions: 2 ft. 4 in. L x 1 ft. 1 in. W x 1 ft. 4 in. H. (ACN 42). FAD

