

GEA FES 270-ME / Mycom 200L Screw Compressor Package - 350 HP

Mfg: Mycom



Model: 270-ME / 200L

Stock No.: HDCF198.75a

Serial No.: 2012630

GEA FES 270-ME / Mycom 200L Screw Compressor Package. Model: 270-ME / 200L. S/N: 2012630. Refrigerant: ammonia. Rated at 239 tons at 342 BHP for (+10°) suction and 96°F condensing. Leak test pressure: 313 psig. Hydrostatic test pressure: 470 psig. E.L. Nickell oil separator, S/N: 22753, Nat'l Bd: 20782, MAWP: 250 psi, maximum temperature: 650 °F, minimum design metal temperature: -20 °F, shell thickness: 1/4 in., head thickness: 5/16 in., radius: 2:1. Toshiba Induction motor, 350 hp, 3540 rpm, 460 V, 380 amps, 60 Hz, 3 phase. GEA FES Micro III Control panel, Model: Retrofit Panel, S/N: 003039102, control power supply: 120 V, 25 FLA, 60 Hz, single phase. FES/York Rotary positive displacement pump, S/N: 10996188, P/N: 290-000030-022. General Electric motor, 5 hp, 1150 rpm, 230/460 V, 16.2/8.1 amps, 60 cycles, 3 phase. Displacement: 853 cfm. Vi setting: 3.6. Inlets: (1) 6 in. dia. refrigerant suction port. Outlets: (2) 1 in. dia. ports (pressure relief valves), (1) 4 in. dia. refrigerant discharge port. Overall dimensions: 11 ft. 10 in. L x 4 ft. W x 8 ft. 4 in. H.(ACN 800-72).







GEA Refrigeration Division **FES Systems Inc.**

FES Contract No. 03039102

Model No. RETROFIT PANEL

Serial No. 03039102

Electrical Inspection by G. GORHAM

Date 11-18-02

York, PA USA
010-62314-900



The following pictures are from the previous installation.

