

Blackmer Dover Sliding Vane Liquefied Gas Pump LGL Series

Mfg: Blackmer Dover

Model: LGL 1-1/2

Stock No: HDCF211.6

Serial No: 217008I

Blackmer Dover Sliding Vane Liquefied Gas Pump. Model: LGL 1-1/2. S/N: 217008I. ID No: 41Q-1. Flow rate for a new pump: 37 gpm. Baldor Industrial Motor: 2 hp, 208-230/460 V, 6.5-6.2/3.1 amps, 60 Hz, 3 phase. Inlets: (1) 1-1/2 in. dia. FNPT. Outlets: (1) 1 in. dia. FNPT, (1) 1/2 in. dia. press. relieve valve. Designed for medium capacity requirements such as auto propane dispensing and multiple scale bottle filling applications, the LGL series of pumps have built in relief valves to protect downstream piping systems by using external bypass valves to set discharge pressure. The LGL also features a redesigned, cavitation suppression liner. Overall dimensions: 2 ft. L x 1 ft. 3-1/2 in. W x 1 ft. 4 in. H.(ACN26-87).

