

**Reco NSV-324B / Frick RDB-134 Booster Rotary Screw Compressor Package – 125 HP**

**Mfg: Reco / Frick**

**Model: NSV-324B / RDB-134**

**Stock No: KWBF163.35**

**Serial No: 19025-300**

Reco NSV-314B / Frick RDB-134 Booster Rotary Screw Compressor Package. Model: NSV-314B / RDB-134. S/N: 19025-300. Same machine as FRICK RDB-134. Frick rotary screw compressor, Model/SN: GDLS193L0004QQ. Maximum speed: 4500 rpm. Design pressure: 362. Vi setting: 2.8. Displacement: 790 cfm. Refrigerant: last used with R-717 (Ammonia). Toshiba electric motor, Model: B1252VLG3UD, S/N: 9609351A, 125hp, 3535 rpm, 292/146 amps, 230/460 V, 60 Hz, 3 phase. Oil Separator, SN: 19025-290-A. MAWP: 150 psig @ 300°F 225 test psig. MDMT: -20° F @ 150 psig. Radius: 2:1 elliptical ends. 1995 Chil-Con oil cooler, Model: TS00-037-06084. SN: C950709A-1. Shell side MAWP: 400 psi @ 200°F. Shell side MDMT: -20°F @ 400 psi. Tube side MAWP: 300 psi @ 200°F. Tube side MDMT: -20°F @ 300 psi. Reco oil filter. SN: M908-370°F. MAWP: 350 psig @ 300°F. MDMT: -20°F @ 350 psig. Test pressure: 525 psig. Blackmer oil pump, Model: XLSF1 1/2N, SN: 269193 N. ID: 41R1. Baldor industrial motor, 3hp, 1725 rpms, 8.4-8.2/4.1 amps, 208-230/460 V, 60Hz, 3 phase. Reco control panel. Control voltage: 120V. Compressor run time: 203.3 hrs. We are not sure if that is original hours, hours since last rebuild, or hours since a new meter has been installed. Overall dimensions 9 ft. 11 in. L x 4 ft. 4 in. W x 8 ft. 3 in. H.











