

Toshiba High Efficiency Electrical Motor -200 HP

Mfg: Toshiba

Model: B2002VLG3US

Stock No: KWBF503A

Serial No: 97310403

Toshiba High Efficiency Electrical Motor – 200 HP. Model: B2002VLG3US. S/N: 97310403. Motor specifications: 3570 rpm, 230/460 V, 235/470 amps, 60 Hz, 3 phase. Frame: 444TS. Insulation class: F. Nema design: B. Code: G. Type: TIKK. Shaft diameter: 2 .375 in. Motor was made in the USA. Overall dimensions: 2 ft. 10 in. L x 2 ft. 9 in. W. x 2 ft. 2 in. H. (ACN93)



