

## 2003 Frick Ammonia Oil Separator- 400 HP

**Mfg: Frick**

**Model:**

**Stock No. HDKF722.79**

**Serial No.**

2003 Frick Ammonia Oil Separator- 400 HP. S/N: 112535. Shell side MAWP: 300 psi, shell side MDMT @ 10.2 psi: -20 °F. Frick Oil Cooler, S/N: MCMC94003, Nat'l Bd: 114118, shell side MAWP @ 200°F: 350 psi, shell side MDMT @ 10.2 psi : -20 °F, tube side MAWP 200 °F: 300 psi, tube side MDMT @ 10.2 psi : -20 °F. Frick RWB II Plus Control Panel with touchpad controls and digital display, electrical requirements: 120 V, 25 amps, 50/60 Hz, single phase. Viking Rotary Pump. U.S. Motor, 7.5 hp, 1165 rpm, 230/460 V, 20.2/10.1 FLA, 60 Hz, 3 phase. Ram High Efficiency Motor, 400 hp, 3565 rpm, 2300/4160 V, 91/51 amps, 60 Hz. Inlets: (1) 20 in. dia. suction port with a 23 in. dia. flange and (18) 1 in. dia. attachment holes at a center-to-center distance of 3-1/2. Outlets: (1) 8 in. dia. discharge port. Overall dimensions: 18 ft. L x 82 in. W x 12 ft. 4 in. H.





