

## U.S. Electric Motor- 10 HP

**Mfg: U.S. Electric**

**Model: F824**

**Stock No.: KWBF750P**

**Serial No.:**

U.S. Electric Motor- Model: F824. Reference No. R92371AE901. Motor specifications: 10 hp, 1740 rpm, 208-230/460 V, 28.0-26.0/13.0 amps, 60 Hz, 3 phase. Frame: L215T. Insulation class: FP. Nema design: B. Code: H. Shaft diameter: 1-1/2 in. Overall dimensions: 1 ft. 11 in. L x 1 ft. W x 1 ft. 10 in. H.



