

## FES Mycom 200S Twin Screw Compressor Package-250 HP

Mfg: FES Mycom

Model: 180-E/200S

Stock No.: HDKF723.17

Serial No.: 2052907

FES 180-ME / Mycom 200S Screw Compressor Package - 250 HP. Model: 180-ME / 200S. S/N: 2052907. Leak pressure: 313 psig. Hydrostatic pressure: 470 psig. FES Oil Separator, S/N: 75044, Nat'l Bd: 88, MAWP: 250 psi @ 300 °F, MDMT: -20 °F @ 250 psi, head radius: 2:1, head thickness: 5/16 in., shell thickness: 5/16 in. Reco Oil Cooler, S/N: M901800C, Nat'l Bd: 5891, MAWP: 350 psi @ 300°F. MDMT: -20 °F @ 250 psi. Toshiba Motor, 250 hp, 3535 rpm, 230/460 V, 572/286 amps, 60 Hz, 3 phase. Displacement: 571 cfm. Inlets: (1) 5-1/2 in. dia. suction port with a 10 in. dia. flange and (8) 3/4 in. dia. attachment holes at a center-to-center distance of 8-1/2 in. Outlets: (1) 3 in. dia. discharge port with a 6 in. L x 6 in. W square flange and (4) 3/4 in. dia. attachment holes at a center-to-center distance of 4-1/2 in. Viking Rotary Pump, Model: AK195, S/N: 1038084. Toshiba Motor, 5 hp, 1155 rpm, 230/460 V, 14.0/7.0 amps, 60 Hz, 3 phase. Cutler Hammer Starter Control Panel. S/N: 4AF773915. Dwg. No: LRA.1825. MTC 3KVA Transformer, 460 V, 50/60 Hz, 60 Hz, 3 phase. Panel dimensions: 3 ft. L x 1 ft. 10 in. W 7 ft. 10 in. H. Overall dimensions: 11 ft. 8 in. L x 6 ft. 6 in. W x 7 ft. 10 in. H. Compressor run time: 2,865.(ACN630).





