

Fristam FPX-Series Centrifugal Pump

Mfg: Fristam

Model: FPX701

Stock No. HDPH036.3a

Serial No. FPX70197517

Fristam FPX-Series Centrifugal Pump. Model: FPX701. S/N: FPX70197517. Capacity: 15 gpm @ 13 ft. Impeller diameter: 3-15/16 in. Baldor Industrial Motor, 1 hp, 1725 rpm, 208-230/460 V, 3.5-3.2/1.6 amps, 60 Hz, 3 phase. The FPX Series sanitary centrifugal pump has become an industry standard for most general applications. Capable of delivering high volumes and high pressures while handling shear sensitive products, it is the pump of choice for products with viscosities up to 600 cps and process temperatures up to 400°F. The FPX series is well known for quiet, efficient, low maintenance operations and is completely CIP'able. Inlets/outlets: (2) 1-1/2 in. dia. S-line fittings. Overall dimensions: 23 in. L x 11-1/2 in. W x 9-1/2 in. H.



