

Fristam FPX Centrifugal Pump

Mfg: Fristam

Model: FPX70199

Stock No. HDPH434.3

Serial No. FPX70197516

1997 Fristam FPX Centrifugal Pump. Model: FPX70199. S/N: FPX70197516. Capacity: 7 gpm. Seal option: single mechanical seal. Impeller diameter: 4 in. The FPX Series sanitary centrifugal pump has become an industry standard for most general applications. Fristam FPX series pumps offer gentle product handling and internal seals for longer seal life. These pumps are capable of product temperatures up to 400 °F. Fully CIP-able and SIP-able. Possible applications: beverages, syrup, milk, creams. Baldor Industrial Motor, 1 hp, 1725 rpm, 208-230/460 V, 3.5-3.2/1.6 amps, 60 hz, 3 phase. Inlets/outlets: (2) 1-1/2 in. dia. S-line fittings. Overall dimensions: 2 ft. L x 8-1/2 in. W x 1ft. H. (ACN20).



