

Aurora Centrifugal Pump

Mfg: Aurora

Model:

Stock No. HDPP910.1

Serial No.

Aurora Centrifugal Pump. Type: 411 BF. No: 89-13246. Size: 4x5x11. Capacity: 578 gpm at 80 feet. Maximum impeller diameter: 11 in. Typical applications include: cooling and heating in air conditioning service, boiler feed service, condensate service, and high pressure water service. Magnetek AC Motor, 20 hp, 1750 rpm, 208-230/460 V, 53-50/25 amps, 60 Hz, 3 phase. Inlet: (1) 6 in. diameter. Outlet: (1) 6 in. diameter. Overall dimensions: 73 in. L x 53 in. W x 39 in. H.



