

1993 Vilter VSS601 Single Screw Compressor Package – 250 HP

Mfg: Vilter

Model: VSS601

Stock No: MDBC301

Serial No:

1993 Vilter VSS601 Single Screw Compressor Package. Model: VSS601. Refrigerant: Last used with R-717 (ammonia). Nominal capacity: 214 tons at 227.9 bhp with a 20°F suction temperature and a 95°F condensing temperature. Variable Vi setting: 2.2 to 5.0. Displacement: 568 cfm. 250 HP electric motor. 1993 Vilter oil separator, National Board No: 38902. S/N: 3-47804-2. MAWP: 300 psig at 400 °F. MDMT: -20°F at 300 psi. Inside straight-wall dimensions: 1 ft. 8 in. dia. x 10 ft. 9 in. L. Viking pump, model: HV2657-2501-A, ser: 10466104. Baldor DC motor, 1 hp, 1750 rpm, 90 V. Hydraulic pump, Century AC motor, 3/4 hp, 1725 rpm, 200-230/460 V, 2.3-2.4/1.2 amps, 60 Hz, 3 phase. Vilter microprocessor control panel. Inlet: (1) 4 in. dia. port. Outlet: (1) 4 in. dia. port. Weight: 6,140 lbs. Overall dimensions: 12 ft. 7 in. L x 4 ft. 3 in. W x 7 ft. 5 in. H. No hours on compressor since factory rebuild. (ACN815)







