

2000 Twin Heat Exchanger System

Mfg:	Model:
Stock No. MFBB359a.0	Serial No. 3129 and 3128

2000 Twin Heat Exchanger System. S/N 3129 and 3128. Natl board #: 3327 and 3326. (32) 304 Stainless steel tubes. Tube diameter: ½ in. Tube length: 31 in. Shell: cast nickel. Shell dia: 6-1/2 in. Shell and tube side MAWP: 150 psi @ 375 °F. Shell and tube side MDMT: 150 psi @ -20 °F. Meters/controls: (4) Worcester Actuators, Series 39, (6) Fischer Model 1-1/4 in., (2) El-O-Matic Actuators Type ESA-65-4/A. 1st Heat Exchanger Inlet gauge: 100 psi max. Outlet gauge: 200 psi max. 2nd Heat Exchanger Inlet gauge: 100 psi max. Outlet gauge: 160 psi max. (2) Bell and Gosset Pumps, S/N22952 and 2296249, 5 hp, 208-230/460 V, 3465 rpm. Capacity: 60 gpm. Overall dimensions: 138 ft, 7 in. L x 39 in. W x 80 in. H.

