

1992 Chester Jensen Falling Film Plate Chiller

Mfg: Chester Jensen

Model:

Stock No. HDWR311.10

Serial No. 9203-CP

1992 Chester Jensen Falling Film Plate Chiller. S/N: 9203-CP. S/N's (plates): 58678, 58683, 58681, 58679, 58680, 58682. Nat'l Bd. No's (plates): 18362, 18364, 18365, 18360, 18361, 18363. Number of plates: 12. Plate dimensions: 5 ft. 2 in. L x 3 ft. 11 in. H. Number of corrugations: 32. Reservoir Tank- 250 Gallon, inside straight-wall dimensions: 6 ft. 4 in. L x 5 ft. W x 1 ft. 1 in. H. Inlets: (1) 4 in. dia. liquid infeed port, (1) 4 in. dia. wet suction port, (1) 3/4 in. dia. port, (1) 4 in. dia. product infeed. Outlets: (1) 2 in. dia. vent port, (1) 4 in. dia. drain port. Overall dimensions: 8 ft. 10 in. L x 5 ft. 4-1/2 in. W x 7 ft. 6 in. H.

1992 Donlee Corporation Horizontal Surge Drum- 200 Gallon. S/N: 060192. Inside straight-wall dimensions: 2 ft. 6-1/2 in. dia. x 5 ft. 8 in. L. MAWP: 150 psi @ 100°F. MDMT: -20°F @ 100 psi. Head thickness/material: 0.250 in./SA 516-70. Shell thickness/material: 0.3125 in./SA36. Parker Float Switch, 120/240 VAC, 7 amp, max temp: 150°F. Refrigerant Specialties Co. Solenoid Valve, S/N: V18280. Refrigerant Specialties Co. Pressure Regulator, S/N: W09757, type: A4A. (2) Parker Pressure Relief Valves, S/N: 0019875, 00119866, Type: SRH1, set pressure: 150 psig, air capacity: 464 scfm. Inlets: (1) 1 in. dia. liquid inlet, (1) 4 in. dia. wet suction port. Outlets: (1) 4 in. dia. compressor suction port, (1) 4 in. dia. liquid outlet port, (1) 1/2 in. dia. oil drain port. Overall dimensions: 7 ft. 4 in. L x 3 ft. 4 in. W x 14 ft. 3 in. H.













