

Copeland Air Cooled Condensing Unit - 5 Ton

Mfg: Copeland

Model: CSAH-0500-CAB-107N

Stock No.: MHCR303.1a

Serial No.: 64AC1679

Copeland Air Cooled Condensing Unit- 5 Ton. Model: CSAH-0500-CAB-107N. S/N: 64AC1679. Refrigerant: R-12. Copeland 2-Cylinder Reciprocating Compressor, Model: MRF1-0500-CAB, S/N: 64AC1679. Capacity rating: 43,000 Btu's, semi-hermetic, power supply: 230 V, 24.0 FLA, 121 LRA, 60 Hz, single phase. Condenser has 9 fins per inch. Fan diameter: 24 in. Century Electric Fan Motor, 1/3 hp, 825 rpm, 230 V, 2.2 amps, 60 Hz, single phase. (2) Refrigerant Receivers- 3 Gallon (ea), inside straight-wall dimensions: 6 in. dia. x 2 ft, 2 in. L. Inlets: (1) 1-3/8 in. dia. port. Outlets: (1) 1/2 in. dia. compression fitting. Overall dimensions: 3 ft. 4 in. L x 2 ft. 6 in. W x 2 ft. 9 in. H. (ACN55).



