

Chemineer Greerco High Shear Reversible Homomixer

Mfg: Chemineer Greerco

Model: 3HR 95

Stock No: MRDC1165.4

Serial No: 0312-3781 M/C

Chemineer Greerco High Shear Reversible Homomixer. Model: 3HR 95. Serial No: 0312-3781 M/C. Rated capacity: 250 gallons. Mixer features: SS wetted parts, SS cross support, Stellite® bushings, 440 hardened SS rotor-stator, (2) 3 ¾ in. dia. impellers, shaft length: 3 ft. 10 in. Explosion proof Reliance electric motor, 10 hp, 3500 rpm, 230/460 V, 25/12.5 amps, 60 Hz, 3 phase. In addition to being reversible, The design of Greerco high shear mixers exceeds the high quality standards necessary to achieve optimal process results and withstand the rigors of difficult processes that require high shear mixing. Typical applications include solids incorporation, homogeneous dispersions, rapid blending, and particle size reduction. Approximate weight: 420 lbs. Overall dimensions: 3 ft. 5-3/8 in. L x 1 ft. 7 in. W x 7 ft. 6 in. H.







