

Steel Feeder/Hopper – 145 cubic ft.

Mfg:

Model:

Stock No: MRSP120

Serial No:

Steel Feeder/Hopper – 145 cubic ft. capacity, w/ approximately 15 ft. stand. Equipped with: (1) motor driven slide gate, (1) model: R, Roto-Bin-Dicator® for level sensing. Dayton gear motor, 1/6 hp, 40 rpm, 115 V, 4.9 amps, 60 Hz, single phase. Gear ratio: 42.7:1. Final rpm: 1. Torque: 225 in-lbs. (1) 3 ft. L x 1 ft. 5 in. W top access door. Inlet: (1) 10 in. L x 10 in. W port, (1) 5 in. dia. port. Outlet: (1) 8 in. L x 8 in. W port. Overall dimensions: 5 ft. 11 in. L x 5 ft. 7 in. W x 15 ft. 4 in. H. (BH).







