

Auger Stainless Steel

Mfg:

Model:

Stock No. 25.JWIMS-1a

Serial No.

Auger Stainless Steel. Maximum/minimum capacities: 30/20 cu. ft. Auger screw dimensions: 18 in. dia x 12 ft. 4-1/2 in. L. Auger is equipped with a 51 in. L x 41 in. W infeed hopper. Machine uses (2) Parker pneumatic cylinders to open two bottom discharge doors. Dorris Gear Box, 25 ratio. Inlets: 48 in. L x 19 in. W infeed. Outlets 19 in. L x 19 in. W discharge. Overall dimensions: 15 ft. 9 in. L x 41 in. W x 68 in. H.



