

Warren Rupp Sandpiper® Double Diaphragm Pump

Mfg: Warren Rupp Sandpiper

Model: S05B2P2TPNS000

Stock No: MRSP202

Serial No: 1573280

2007 Warren Rupp Sandpiper® Double Diaphragm Pump Model: S05B2P2TPNS000. Approximate pumping capacity: 14 gpm. Pump handles solids up to 0.125 in. (3mm) in size. Operating temperature ranges: 180°F to 32°F. Maximum recommended air pressure: 100 psi. Features a solid ball check valve powered by compressed air and of a 1:1 ratio design. Wetted material: polypropylene. Diaphragm / check valve materials of construction: Virgin PTFE-Santoprene / Backup Virgin PTFE check valve seat: Virgin PTFE. (1) ¾ in. MNPT inlet. (1) ¾ in. MNPT outlet. (1) ½ in. FNPT airline inlet. Overall pump dimensions: 10-1/8 in. L. x 7-1/8 in. W. x 11-3/4 in. H. (ACN7)

