

2006 Warren Rupp Sandpiper® Double Diaphragm Pump


Mfg: Warren Rupp


Model: S1FB3P1PPUS000

Stock No: MRSP220.a

Serial No: 1501698

2006 Warren Rupp Sandpiper® Double Diaphragm Pump. Model: S1FB3P1PPUS000. S/N: 1501698. Maximum recommended air pressure: 100 PSI. Inlet/outlet: (2) 1-1/8 in. inner flange dia. with (4) 3/4 in. mounting holes. 2-3/8 in. adjacent, 3-1/4 in. opposite. (1) 3/4 in. FNPT air inlet. Overall dimensions: 1 ft. 5 in. L x 1 ft. W x 1 ft. 9 in. H.





SANDPIPER

S1FB3P1PPUS000.

Serial #: 1501698

Date: 10-06-2006

Maximum Recommended Air Pressure:
100 PSI - 7 BAR

WARREN RUPP A Unit of
IDEX Corporation



535-069-000

U.S. Patent #5,996,627