

1992 Morfab Company, Inc. Low Pressure Ammonia Receiver – 20 in. Dia. x 8 ft. 6 in. L

Mfg: Morfab Company, Inc.

Model:

Stock No: LCNM012

Serial No: 4763

1992 Morfab Company, Inc. Low Pressure Ammonia Receiver. S/N 4763. Nat'l Bd: 3763. Approximate capacity: 145 gallons. Vessel dimensions: 20 in. dia. x 8 ft. 6 in. H. MAWP 250 psi at 650 °F. MDMT 60 °F at 100 psi. Parker RSF, size: 1/2 in. (13 mm). Hansen solenoid valve, model: HS4A L09F, size: 3/4 in. Inlet: (1) 4 in. refrigerant inlet. Liquid level column with isolation valves. Column dimensions: 10 in. dia. x 5 ft. 4 in. H. Armored liquid level gauge. Gauge dimensions: 9 in. dia. x 4 ft. 6-1/2 in. H. Overall dimensions: 6 ft. 4 in. L x 4 ft. 10 in. W x 9 ft. 2 in. H. (ACN72)



