

Warren Rupp Sandpiper® Double Diaphragm Pump



Mfg: Warren Rupp

Model: PB1-A

Stock No: MRSP284.a

Serial No: 331008

Warren Rupp Sandpiper® Double Diaphragm Pump. Model: PB1-A. S/N: 331008. Type: TGN-1-PP. Maximum recommended air pressure: 100 PSI. Inlet/outlet: (2) 1-1/4 in. NPT. (1) 3/4 in. FNPT air inlet. Overall dimensions: 1 ft. 3 in. L x 10-1/2 in. W x 1 ft. 7 in. H.



SandPIPER®

AIR-POWERED DOUBLE DIAPHRAGM PUMP

000-015-000

MODEL PB1-A

TYPE TGN-1-PP

SERIAL 331008

Maximum Recommended Air Pressure: 100 psi
Manufactured in the U. S. A. by

WARREN A Unit of **IBEX** Corporation
14901 1568