



- NOTES:**
1. (M) - FAN MOTOR LOCATION
  2. MAKE-UP WATER PRESSURE 20psi MIN. 50psi MAX.
  3. 3/4" DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DWG.
  4. HEAVIEST SECTION IS COIL SECTION.
  5. ALL NIPPLE LOCATIONS ARE APPROXIMATE DIMENSIONS. DO NOT USE FOR PREFABRICATION OF CONNECTING PIPING.

MODEL	WEIGHTS			DIMENSIONS			NO. SHIPPING SECTIONS
	SHIPPING	OPER.	HEAVIEST SECTION (4)	H	C	R	
PMCB 455	17360	23440	12940	13'-11-3/4"	5'-4-3/4"	39'-1/4"	2

CERTIFIED FOR APV CREPACO PROJECT: PURE MILK DAIRY  
 CUSTOMER ORDER NO. 38-89601  
 CAPACITY 323 T.R.  
 FAN MOTOR (1) 20 TEFC  
 PUMP MOTOR (1) 5  
 REMARKS DRIVE SIZED FOR 0" ESP.

EVAPCO NO. 953317M TAG  
 REFRIG. 96.3 \*COND 20 \*SUCTION 78 \*W.B.  
 H.P. ELEC. SPEC. 460/60/3  
 H.P. ELEC. SPEC. 460/60/3



EVAPORATIVE CONDENSER

REV 4/18/95 JR DATE

CP1012BA-B01S