

**Warren Rupp Sandpiper® Double Diaphragm Pump**



**Mfg: Warren Rupp**

**Model: PB1-A**

**Stock No: MRSP222.1**

**Serial No: 381342**

Warren Rupp Sandpiper® Double Diaphragm Pump. Model: PB1-A. S/N: 381342. Type: TGN-2-PP. Maximum recommended air pressure: 100 PSI. Inlet/outlet: (2) 1 in. inner flange dia. with (4) ½ in. dia. mounting holes. 2-1/4 in. adjacent, 3-1/4 in. opposite. (1) ½ in. FNPT air inlet. Overall dimensions: 1 ft. 2-1/2 in. L x 11 in. W x 1 ft. 8 in. H.





**SandPIPER**  
MOTOR-POWERED DOUBLE SANDPUMP SYSTEM

535-015-010

MODEL **PB1-A**  
TYPE **TGN-2-PP**  
SERIAL **381342**

Maximum Recommended Air Pressure: 100 psi  
Manufactured in the U.S.A. by

**WARREN RUPP** A Unit of **BCK** Corporation  
MANSFIELD, OHIO 44901-1568