

## Stainless Steel Shell and Tube Heat Exchanger

Mfg:

Model:

Stock No: NOI172

Serial No:

Stainless Steel Shell and Tube Heat Exchanger. Tube material: 316 stainless steel. Number of passes: 12. Number of tubes: 48. Tube dimensions: 1-1/2 in. dia. x 10 ft. 1-1/2 in. L. Heat transfer surface area: approx. 190.76 sq. ft. Tube volume: 44 gal. Inlets: (1) 1-1/2 in. dia. S-line fitting (product), (1) 1-1/2 in. dia. MPT (media). Outlets: (1) 1-1/2 in. dia. S-line fitting, (1) 1 in. dia. MPT (media). Overall dimensions: 11 ft. 4 in. L x 3 ft. 2 in. W x 8 ft. H.

