

Warren Rupp Sandpiper® Double Diaphragm Pump

Mfg: Warren Rupp

Model: PB ½ -A

Stock No: MRSP278.a

Serial No: 586646

Warren Rupp Sandpiper® Double Diaphragm Pump. Model no. PB ½ -A. Serial no. 586646. Type: TGN-3-PP. Maximum recommended air pressure: 100 psi. Features a solid ball check valve powered by compressed air and of a 1:1 ratio design. (1) ¾ in. MNPT inlet. (1) ¾ in. MNPT outlet. (1) ½ in. FNPT airline inlet. Overall dimensions: 10-1/8 in. L. x 7-1/8 in. W. x 11-1/2 in. H.



